

Parallel kit
EAMM-U-86-S48-70GA-102
Part number: 8059000

FESTO



Data sheet

Feature	Value
Size	86
Mounting position	optional
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	175 kgmm ²
Frictional torque independent of load	0.25 Nm
Transmittable torque	9.5 Nm
Product weight	2500 g
Interface code, actuator	S48
Interface code, motor in	70GA
Note on materials	RoHS-compliant