


Parallel kit
EAMM-U-110-D50-120GA-120
Part number: 8059040

FESTO



Data sheet

Feature	Value
Size	110
Mounting position	optional
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	799 kgmm ²
Frictional torque independent of load	0.3 Nm
Transmittable torque	9.5 Nm
Product weight	5250 g
Interface code, actuator	D50
Interface code, motor in	120GA
Note on materials	RoHS-compliant