

Plastic tubing PTFEN-14X2-NT

Part number: 8061176

FESTO



Data sheet

Feature	Value
Outside diameter	14 mm
Flow-relevant bending radius	120 mm
Inside diameter	10 mm
Min. bending radius	106 mm
Instructions on use	Tubing without printing
Operating pressure complete temperature range	-0.095 MPa...0.5 MPa -0.95 bar...5 bar -13.775 psi...72.5 psi
Temperature-dependent operating pressure	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Fire test material	UL94 V-0
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Element installed statically, no meaningful evaluation possible according to ISO 14644-1
Suitable for use with food	See supplementary material information
Ambient temperature	-20 °C...150 °C
Product weight according to length	0.162 kg/m
Pneumatic connection	For push-in connector outer diameter of 14 mm
Colour	Natural
Shore hardness	D 55 +/-5
Note on materials	RoHS-compliant
Material tubing	PTFE