

Fixed flow restrictor-SET VFFG-T-F6-A-V1

Part number: 8062201

FESTO



Data sheet

Feature	Value
Valve function	Flow control function
Type of mounting	Tapped
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Ambient temperature	-5 °C...60 °C
Approval	c UL us - Recognized (OL)
Size	For ø 5.8 mm
Nominal size	0.7 mm...1.8 mm
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C...40 °C
Note on materials	RoHS-compliant