


Axial kit
EAMM-A-L27-50GA
Part number: 8063454



Data sheet

Feature	Value
Nominal length	26.6 mm
Mounting position	optional
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	0.45 kgmm ²
Transmittable torque	2 Nm
Product weight	249 g
Interface code, actuator	L27
Interface code, motor in	50GA
Note on materials	RoHS-compliant