


**Axial kit**  
**EAMM-A-M48-90GB**  
Part number: 8063558



**Data sheet**

| Feature                  | Value                |
|--------------------------|----------------------|
| Nominal length           | 31.5 mm              |
| Mounting position        | optional             |
| Max. rotational speed    | 6000 rpm             |
| LABS (PWIS) conformity   | VDMA24364-B2-L       |
| Storage temperature      | -25 °C...60 °C       |
| Relative air humidity    | 0 - 95%              |
| Degree of protection     | IP40                 |
| Ambient temperature      | -10 °C...60 °C       |
| Mass moment of inertia   | 39 kgmm <sup>2</sup> |
| Transmittable torque     | 17 Nm                |
| Product weight           | 1022 g               |
| Interface code, actuator | M48                  |
| Interface code, motor in | 90GB                 |
| Note on materials        | RoHS-compliant       |