


Axial kit EAMM-A-M80-75GA

Part number: 8063564

FESTO



Data sheet

Feature	Value
Nominal length	35 mm
Mounting position	optional
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	151 kgmm ²
Transmittable torque	60 Nm
Product weight	1149 g
Interface code, actuator	M80
Interface code, motor in	75GA
Note on materials	RoHS-compliant