


Gear unit
EMGA-80-A-G5-100A
Part number: 8085349

FESTO



Data sheet

Feature	Value
Gear unit flange size	80 mm
Motor flange size	100 mm
Torsional backlash	0.22 deg
Type of gear unit	Right-angle gear unit
Gear unit ratio	5:1
Max. drive speed	7000 rpm
Operating temperature of gear unit	-25 °C...90 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP54
Continuous output torque	67 Nm
Mass moment of inertia of gear unit	1.017 kgcm ²
Max. output torque	107 Nm
Max. efficiency	95 %
Torsional rigidity	4.8 Nm/arcmin
Product weight	4500 g
Gear unit interface, output shaft	80G
Gear unit interface, drive shaft	100A
Note on materials	RoHS-compliant