

**Coupling**  
**EAMD-32-32-14-16X20-U**  
Part number: 8086051

**FESTO**



**Data sheet**

| Feature                | Value                  |
|------------------------|------------------------|
| Mounting diameter 1    | 14 mm                  |
| Mounting diameter 2    | 16 mm                  |
| Size                   | 32                     |
| Nominal length         | 32 mm                  |
| Mounting position      | optional               |
| Max. rotational speed  | 8000 rpm               |
| LABS (PWIS) conformity | VDMA24364-B2-L         |
| Storage temperature    | -25 °C...60 °C         |
| Relative air humidity  | 0 - 95%                |
| Ambient temperature    | -25 °C...60 °C         |
| Mass moment of inertia | 14.5 kgmm <sup>2</sup> |
| Transmittable torque   | 16 Nm                  |
| Product weight         | 124 g                  |
| Note on materials      | RoHS-compliant         |