

# Pressure gauge PAGN-26-10-P10-RG

Part number: 8090378

**FESTO**



## Data sheet

| Feature                             | Value                                                   |
|-------------------------------------|---------------------------------------------------------|
| Indicating range                    | 0 bar...10 bar<br>0 MPa...1 MPa                         |
| Nominal size of pressure gauge      | 26                                                      |
| Design                              | Bourdon tube pressure gauge without measuring mechanism |
| Type of mounting                    | In-line installation                                    |
| Operating medium                    | Inert gases<br>Neutral fluids                           |
| Note on operating and pilot medium  | No acetylene<br>No oxygen                               |
| Operating pressure                  | 0 MPa...1 MPa<br>0 bar...10 bar<br>0 psi...145 psi      |
| Alternating load factor             | 0.66                                                    |
| Measurement accuracy class          | 4                                                       |
| Degree of protection                | IP43                                                    |
| Storage temperature                 | -5 °C...50 °C                                           |
| Media temperature                   | -20 °C...60 °C                                          |
| Ambient temperature                 | -20 °C...60 °C                                          |
| LABS (PWIS) conformity              | VDMA24364-B1/B2-L                                       |
| Note on materials                   | RoHS-compliant                                          |
| Position of connection              | Centred, rear side                                      |
| Pneumatic connection                | Cartridge 10 mm                                         |
| Material in contact with the medium | Brass                                                   |
| Material screwed plug               | Brass                                                   |
| Material housing                    | PA                                                      |
| Material screen                     | PS                                                      |
| Housing colour                      | Black                                                   |
| Product weight                      | 15 g                                                    |
| Scale                               | Double scale<br>MPa (internal)<br>Bar (outside scale)   |