

Service unit
MS6-EM1FR-1/2-D6-C-P-M-AG-MPA-WPE-B
 Part number: 8098371

FESTO



Data sheet

Feature	Value
Size	6
Series	MS
Mounting position	Vertical +/-5°
Pressure gauge (ANALOG) or Pressure display (DIGITAL)	With pressure gauge
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar 14.5 psi...145 psi
Standard nominal flow rate, exhaust 0.6->0 MPa (6->0 bar, 87->0 psi)	3600 l/min
Standard nominal flow rate (standardised to DIN 1343)	4750 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Compatibility with ester oil not guaranteed
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-5 °C...50 °C
Media temperature	-5 °C...50 °C
Ambient temperature	-5 °C...50 °C
Product weight	1250 g
Type of mounting	In-line installation Via mounting bracket With accessories Either:
Note on materials	RoHS-compliant