

Clamping sleeve
EAMH-145-22-C34
Part number: 8098588



Data sheet

Feature	Value
Size	145
Mounting position	optional
Max. rotational speed	4000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	32.5 kgmm ²
Product weight	198 g
Note on materials	RoHS-compliant