

# Connector plate VABS-B14-T-FG14

Part number: 8098884

FESTO



## Data sheet

| Feature                        | Value                                      |
|--------------------------------|--------------------------------------------|
| Mounting position              | optional                                   |
| Design                         | Connection orientation up                  |
| Operating pressure             | 1.5 bar...10 bar                           |
| Operating medium               | Compressed air to ISO 8573-1:2010 [7:...]  |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress              |
| LABS (PWIS) conformity         | VDMA24364 zone III                         |
| Storage temperature            | -20 °C...60 °C                             |
| Media temperature              | -20 °C...60 °C                             |
| Ambient temperature            | -20 °C...60 °C                             |
| Product weight                 | 192 g                                      |
| Type of mounting               | With through-hole                          |
| Pneumatic connection, port 2   | Flange 1/4 with NAMUR port pattern<br>G1/4 |
| Pneumatic connection, port 4   | Flange 1/4 with NAMUR port pattern<br>G1/4 |
| Note on materials              | RoHS-compliant                             |
| Material sub-base              | Wrought aluminium alloy                    |