

Connector plate VABS-B14-T-FN14

Part number: 8099628

FESTO



Data sheet

Feature	Value
Mounting position	optional
Design	Connection orientation up
Operating pressure	1.5 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:...]
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...60 °C
Media temperature	-20 °C...60 °C
Ambient temperature	-20 °C...60 °C
Product weight	192 g
Type of mounting	With through-hole
Pneumatic connection, port 2	Flange 1/4 with NAMUR port pattern 1/4 NPT
Pneumatic connection, port 4	Flange 1/4 with NAMUR port pattern 1/4 NPT
Note on materials	RoHS-compliant
Material sub-base	Wrought aluminium alloy