

Position indicator SAMH-F12-MK-A2

Part number: 8101084

FESTO



Data sheet

Feature	Value
Mounting position	optional
Design	2 proximity switches with explosion protection and high level of IP protection
Explosion protection	Zone 2 (ATEX) Zone 22 (ATEX)
Instructions on use	The SIL certification for the entire product is invalidated when used with angle seat valve VZXA.
Note on materials	RoHS-compliant
Ambient temperature	-20 °C...60 °C
Storage temperature	-10 °C...60 °C
Product weight	151 g
Material seals	EPDM
Material housing	Aluminium PA-reinforced
Degree of protection	IP65 IP67
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III