

Fitting

NLFA-D-U14-B2.1-PP-P10

Part number: 8104289

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size of pack | 10 |
| Design | Tubing mount via barbed connector Straight design |
| Size | ø 8 mm |
| Fluid connection | UNF1/4-28 |
| Fluid connection 2 | For tubing I.D. 2.1 mm |
| Medium | Liquid media Gaseous media |
| Note on the medium | Observe resistance of materials that come into contact with the media |
| Operating pressure complete temperature range | -0.075 MPa...0.4 MPa -0.75 bar...4 bar -10.875 psi...58 psi |
| Media temperature | 0 °C...35 °C |
| Ambient temperature | 0 °C...35 °C |
| Storage temperature | -20 °C...70 °C |
| Sealing principle | Hard |
| Mounting position | optional |
| Nominal torque | 15 Ncm |
| Tolerance for nominal tightening torque | ± 15% |
| Product weight | 0.5 g |
| Material in contact with the medium | PP |
| Material screwed plug | PA-reinforced |
| Note on materials | RoHS-compliant |
| Suitable for use with food | See supplementary material information |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Instructions on use | See application note (available on the Support Portal at festo.com) |