


**Parallel kit**  
**EAMM-U-60-S48-60AA-91**  
Part number: 8105898

**FESTO**



**Data sheet**

| Feature                               | Value                  |
|---------------------------------------|------------------------|
| Size                                  | 60                     |
| Mounting position                     | optional               |
| Max. rotational speed                 | 6000 rpm               |
| LABS (PWIS) conformity                | VDMA24364-B2-L         |
| Storage temperature                   | -25 °C...60 °C         |
| Relative air humidity                 | 0 - 95%                |
| Degree of protection                  | IP40                   |
| Ambient temperature                   | -10 °C...60 °C         |
| Mass moment of inertia                | 26.7 kgmm <sup>2</sup> |
| Frictional torque independent of load | 0.07 Nm                |
| Transmittable torque                  | 3 Nm                   |
| Product weight                        | 1150 g                 |
| Interface code, actuator              | S48                    |
| Interface code, motor in              | 60AA                   |
| Note on materials                     | RoHS-compliant         |