

Blanking plug NPQE-P-S16-P5

Part number: 8113209

FESTO



Data sheet

Feature	Value
Size	Standard
Mounting position	optional
Design	Blanking plug
Size of pack	5
Operating pressure complete temperature range	-0.095 MPa...0.8 MPa -0.95 bar...8 bar -13.775 psi...116 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Cleanroom class	Element installed statically, no meaningful evaluation possible according to ISO 14644-1
Ambient temperature	-5 °C...60 °C
Product weight	5.07 g
Pneumatic connection, port 1	Push-in sleeve Ø 16 mm
Colour of release ring	Blue
Note on materials	RoHS-compliant
Material housing	PBT
Material release ring	POM