

Safety clip
NPAP-QE-S-Q12-P10
Part number: 8113232

FESTO



Data sheet

Feature	Value
Size of pack	10
Mounting position	optional
Operating pressure complete temperature range	-0.095 MPa...0.8 MPa -0.95 bar...8 bar -13.775 psi...116 psi
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Cleanroom class	Element installed statically, no meaningful evaluation possible according to ISO 14644-1
Ambient temperature	-5 °C...60 °C
Product weight	0.28 g
Pneumatic connection	For tubing O.D. 12 mm
Note on materials	RoHS-compliant