



Pilot valve

MGXDH-3/2-1.2-230AC-KS

Part number: 8118344

FESTO



Data sheet

Feature	Value
Valve function	3/2-way, closed, monostable
Type of actuation	Electric
Operating pressure	-0.09 MPa...0.8 MPa -0.9 bar...8 bar -13.05 psi...116 psi
Design	On/off valve
Type of reset	Mechanical spring
Certificate issuing authority	21-GA4B0-0068X 21-GA4B0-0069X
Explosion ignition protection type for gas	Ex db IIC T6...T3 Gb
Explosion ignition protection type for dust	Ex tb IIIC T85°C Db
Explosion ambient temperature	-65°C ~+40°C T4 -65°C ~+55°C T3
Degree of protection	IP66
Manual override	Detenting
Flow direction	Non-reversible
Duty cycle	100%
Insulation material class	H
Characteristic coil data	230 V AC: 50/60 Hz, initial power: 9.5 VA, holding power: 6.0 VA
Permissible frequency fluctuations	+/- 10%
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-20 °C...80 °C
Type of mounting	CNOMO
Note on materials	RoHS-compliant