

Gripper jaws DHAS-GG-B18-16-A1

Part number: 8119108

FESTO



Data sheet

Feature	Value
Size	16 mm
Mounting position	optional
Design	For microwell plates
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-20 °C...70 °C
Relative air humidity	0 - 100%
Ambient temperature	0 °C...40 °C
Product weight	24.4 g
Type of mounting	With female thread M3
Note on materials	RoHS-compliant
Material gripper jaws	High-alloy stainless steel
Material cylindrical dowel pin	Spring steel