

Retainer VMPA2-FTI

Part number: 8129128

FESTO



Data sheet

Feature	Value
Size	20
Mounting position	optional
Size of pack	10
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar -13.05 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C...40 °C
Media temperature	-5 °C...60 °C
Ambient temperature	-5 °C...60 °C
Product weight	0.12 g
Type of mounting	Clamped
Note on materials	RoHS-compliant
Material retaining bracket	POM