


Gear unit

EMGA-60-A-G12-60P

Part number: 8141739

FESTO



Data sheet

Feature	Value
Gear unit flange size	60 mm
Motor flange size	60 mm
Torsional backlash	0.3 deg
Type of gear unit	Right-angle gear unit
Gear unit ratio	12:1
Max. drive speed	13000 rpm
Operating temperature of gear unit	-25 °C...90 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP54
Continuous output torque	44 Nm
Mass moment of inertia of gear unit	0.391 kgcm ²
Max. output torque	70 Nm
Max. efficiency	94 %
Torsional rigidity	2 Nm/arcmin
Product weight	1900 g
Gear unit interface, output shaft	60G
Gear unit interface, drive shaft	60P
Note on materials	RoHS-compliant