

Reducing nipple NPFC-RS-G1-G3/4-MF

Part number: 8142602

FESTO



Data sheet

Feature	Value
Material threaded fitting	Nickel-plated brass
Size of pack	10
Operating pressure	-0.95 bar...10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [:-:-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Nominal tightening torque, pneumatic connection 1	62.5 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	97.09 g
Pneumatic connection, port 1	G1
Pneumatic connection, port 2	G3/4
Note on materials	RoHS-compliant
Material seals	PVC