

**Cable fitting**  
**NETC-M20-PBK-T26-EX4-E**  
Part number: 8151588

**FESTO**



**Data sheet**

| Feature                                           | Value                                                                               |
|---------------------------------------------------|-------------------------------------------------------------------------------------|
| Ambient temperature                               | -40 °C...75 °C                                                                      |
| Degree of protection                              | IP66<br>IP68                                                                        |
| Note on degree of protection                      | IP68 at 5 bar for 30 minutes                                                        |
| ATEX category gas                                 | II 2G                                                                               |
| ATEX category dust                                | II 2D                                                                               |
| Explosion ignition protection type for gas        | Ex eb IIC Gb                                                                        |
| Explosion ignition protection type for dust       | Ex tb IIIC Db                                                                       |
| Explosion ambient temperature                     | -40°C ≤ Ta ≤ +75°C                                                                  |
| Explosion protection certification outside the EU | EPL Db (IEC-EX)<br>EPL Gb (IECEX)                                                   |
| CE mark (see declaration of conformity)           | To EU Explosion Protection Directive (ATEX)<br>In accordance with EU RoHS Directive |
| Size                                              | M20x1.5                                                                             |
| Cable diameter                                    | 4 mm...13 mm                                                                        |
| Colour                                            | Black                                                                               |
| Material cable gland                              | PA                                                                                  |
| Material seals                                    | EPDM                                                                                |
| Product weight                                    | 13 g                                                                                |
| Size of pack                                      | 1                                                                                   |
| LABS (PWIS) conformity                            | VDMA24364 zone III                                                                  |
| Note on materials                                 | RoHS-compliant                                                                      |