

# Connection kit DADG-AK-G8-10-80

Part number: 8152371

FESTO



## Data sheet

| Feature                                       | Value                                                    |
|-----------------------------------------------|----------------------------------------------------------|
| Size                                          | 10                                                       |
| Stroke                                        | 80 mm                                                    |
| Operating pressure                            | 0.1 MPa...0.8 MPa<br>1 bar...8 bar<br>14.5 psi...116 psi |
| Operating medium                              | Compressed air to ISO 8573-1:2010 [7:4:4]                |
| Corrosion resistance class CRC                | 1 - Low corrosion stress                                 |
| LABS (PWIS) conformity                        | VDMA24364-B1/B2-L                                        |
| Ambient temperature                           | -10 °C...60 °C                                           |
| Max. tightening torque                        | 1.5 Nm                                                   |
| Tolerance for tightening torque               | ±10%                                                     |
| Max. tightening torque pneumatic connection 1 | 0.7 Nm                                                   |
| Product weight                                | 14.5 g                                                   |
| Pneumatic connection                          | M5                                                       |
| Material adapter                              | Epoxy resin                                              |
| Material seals                                | NBR                                                      |
| Material screws                               | Coated steel                                             |