

Disposable tip DHAP-300-TA1FS-P960R

Part number: 8160286

FESTO



Data sheet

Feature	Value
Volume	300 µl
Size of pack	960
Design	Pipette tip holder for 20...1000 µl disposable tips from Festo
Packaging type	Rack
Filter	Yes
Bioburden	ATP: < 2 · 10 ⁻¹² mg/µl Free of BSE/TSE DNA: < 32 pg human DNA DNase: ≤ 5 · 10 ⁻⁷ Kunitz units/µl Endotoxin: ≤ 0.001 EU/ml RNase: ≤ 5 · 10 ⁻⁹ Kunitz units/µl
Sterility	SAL 1E-6, pre-sterilised
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	5 °C...40 °C
Note on storage temperature	Short-term for transport in packaging -25 ... 55 °C
Relative air humidity	10 - 90% Non-condensing
Environmental conditions	Atmospheric pressure 80 ... 106 kPa
Ambient temperature	5 °C...40 °C
Note on materials	RoHS-compliant
Pipette tip material	PP