

Coupling
EAMD-56-46-20-23X27-U
Part number: 8165049



Data sheet

Feature	Value
Mounting diameter 1	20 mm
Mounting diameter 2	23 mm
Size	56
Nominal length	46 mm
Mounting position	optional
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	151 kgmm ²
Transmittable torque	65 Nm
Product weight	416 g
Note on materials	RoHS-compliant