

# Exhaust protection VABD-D3-L-GN14

Part number: 8177960



## Data sheet

| Feature                | Value                                                              |
|------------------------|--------------------------------------------------------------------|
| Mounting position      | optional                                                           |
| Operating pressure     | 0 MPa...1 MPa<br>0 bar...10 bar                                    |
| Explosion protection   | Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX) |
| Operating medium       | Compressed air to ISO 8573-1:2010 [7:-:-]                          |
| LABS (PWIS) conformity | VDMA24364 zone III                                                 |
| Degree of protection   | IP54                                                               |
| Ambient temperature    | -50 °C...60 °C                                                     |
| Product weight         | 3.8 g                                                              |
| Type of mounting       | Screw-in<br>Via male thread                                        |
| Note on materials      | RoHS-compliant                                                     |
| Material vent screw    | HP PA 12                                                           |