

# Cartridge NPQX-D-PC19-T38-P10

Part number: 8189810

FESTO



## Data sheet

Feature	Value
Size	Standard
Nominal size	6.4 mm
Tubing insertion depth	20.1 mm
Type of seal on screwed plug	No seal
Mounting position	Horizontal
Design	Straight design Push-pull principle
Size of pack	10
Operating pressure	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Operating pressure complete temperature range	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Product weight	10 g
Type of mounting	Via retaining clamp
Pneumatic connection, port 1	Cartridge 15 mm
Pneumatic connection, port 2	For tubing outside diameter of 3/8"
Colour of release ring	Blue
Note on materials	RoHS-compliant
Material housing	PA-reinforced