

Gripper jaw mounting EHAA-G1-E20-40-GGA1-AP

Part number: 8191126



Data sheet

Feature	Value
Size	40
Mounting position	optional
Design	Vertical gripper mounting
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...70 °C
Relative air humidity	0 - 100%
Ambient temperature	0 °C...40 °C
Product weight	95 g
Note on materials	RoHS-compliant
Material screws	High-alloy stainless steel
Material bracket	High-alloy stainless steel
Material centering elements	High-alloy steel