

Separator VABD-XA-12-P2

Part number: 8191737

FESTO



Data sheet

| Feature | Value |
|------------------------------------|--|
| Size | 12 |
| Pressure-zone division | Ducts 3 and 5 |
| Size of pack | 2 |
| Operating pressure | -0.1 MPa...0.7 MPa -1 bar...7 bar |
| Suitability for vacuum | yes |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -20 °C...70 °C |
| Product weight | 0.5 g |
| Type of mounting | Can be pressed in manually |
| Note on materials | RoHS-compliant |
| Material seals | HNBR |
| Material housing | PA-reinforced |