


Axial kit EAMM-A-D40-60P-G2

Part number: 8197493

FESTO



Data sheet

Feature	Value
Nominal length	51 mm
Mounting position	optional
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	5.87 kgmm ²
Transmittable torque	12.5 Nm
Product weight	340 g
Interface code, actuator	D40 D40C
Interface code, motor in	60P 60PA
Note on materials	RoHS-compliant