


Axial kit
EAMM-A-D50-60G-S1-G2
Part number: 8197496



Data sheet

Feature	Value
Nominal length	78 mm
Mounting position	optional
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP65
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	34.8 kgmm ²
Transmittable torque	21 Nm
Product weight	950 g
Interface code, actuator	D50
Interface code, motor in	60G
Note on materials	RoHS-compliant