

# Guide unit FENG-40-50-GF

Part number: 8204069

FESTO



## Data sheet

| Feature                  | Value                                                |
|--------------------------|------------------------------------------------------|
| Size                     | 40                                                   |
| Stroke                   | 50 mm                                                |
| Mounting position        | optional                                             |
| Guide                    | Plain-bearing guide                                  |
| Design                   | Guidance                                             |
| Explosion protection     | The information in the certificate must be observed! |
| LABS (PWIS) conformity   | VDMA24364-B2-L                                       |
| Ambient temperature      | -20 °C...80 °C                                       |
| Displacement force       | 30 N                                                 |
| Moving mass              | 937 g                                                |
| Product weight           | 2635 g                                               |
| Type of mounting         | Via female thread                                    |
| Note on materials        | RoHS-compliant                                       |
| Material guide component | High-alloy steel                                     |
| Material housing         | Anodised wrought aluminium alloy                     |
| Material yoke plate      | Anodised wrought aluminium alloy                     |