


Coupling hub
EAMC-H-15-7-GB8-5
Part number: 8228647



Data sheet

Feature	Value
Mounting diameter 1	5 mm
Size	15
Nominal length	12.4 mm
Mounting position	optional
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	0.191 kgmm ²
Transmittable torque	1.5 Nm
Product weight	5 g
Note on materials	RoHS-compliant