

Coupling hub
EAMC-H-15-7-GB8-6
Part number: 8228648



Data sheet

Feature	Value
Mounting diameter 1	6 mm
Size	15
Nominal length	12.4 mm
Mounting position	optional
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	0.191 kgmm ²
Transmittable torque	2 Nm
Product weight	5 g
Note on materials	RoHS-compliant