

Coupling hub
EAMC-H-30-10-GB16-9
Part number: 8228656



Data sheet

Feature	Value
Mounting diameter 1	9 mm
Size	30
Nominal length	20.7 mm
Mounting position	optional
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	3.2 kgmm ²
Transmittable torque	8.5 Nm
Product weight	25 g
Note on materials	RoHS-compliant