


On/off valve MS6-EM1-AGF

Part number: 8232876

FESTO



Data sheet

Feature	Value
Series	MS
Size	6
Design	Rotary gate valve
Type of actuation	Manual
Exhaust-air function	Without flow control option
Actuator lock	can be closed with accessories
Type of piloting	Direct
Valve function	3/2 bistable
Operating pressure	0 MPa...1.8 MPa 0 bar...18 bar
C value	30.8 l/sbar
b value	0.57
Standard nominal flow rate (standardised to DIN 1343)	8700 l/min
Standard nominal flow rate 2-3	6200 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4] Inert gases
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Suitable for use with food	See supplementary material information
Type of mounting	Either: In-line installation With accessories
Mounting position	optional
Flow direction	Non-reversible
Product weight	880 g
Pneumatic connection, port 1	G1
Pneumatic connection, port 2	G1
Pneumatic connection, port 3	G1/2

Feature	Value
Material seals	TPE-U(PU)
Material housing	Die-cast aluminium