


Service unit combination

MSB4-1/4:I1:I3

Part number: 8233006

FESTO



Data sheet

Feature	Value
Size	4
Series	MS
Mounting position	Vertical +/- 5°
Condensate drain	Manually rotating
Design	Fibre filter
Max. condensate volume	19 ml
Bowl guard	Plastic bowl guard
Operating pressure	0 MPa...1.4 MPa 0 bar...14 bar 0 psi...203 psi
Max. standard flow rate	360 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [6:::4] Inert gases
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air purity class at output	Compressed air to ISO 8573-1:2010:[5:::3]
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	400 g
Type of mounting	With accessories
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Material seals	NBR
Material filter	Borosilicate fibre
Material housing	Die-cast aluminium
Material bowl	PC