


Service unit combination MSB6-3/8:12:14

Part number: 8233037

FESTO



Data sheet

Feature	Value
Size	6
Series	MS
Mounting position	Vertical +/-5°
Condensate drain	Fully automatic
Design	Fibre filter
Max. condensate volume	38 ml
Bowl guard	Plastic bowl guard
Operating pressure	0.2 MPa...1.2 MPa 2 bar...12 bar 29 psi...174 psi
Max. standard flow rate	900 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [6:-:4] Inert gases
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air purity class at output	Compressed air to ISO 8573-1:2010:[5:-:3]
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	1240 g
Type of mounting	With accessories
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 2	G3/8
Material seals	NBR
Material filter	Borosilicate fibre
Material housing	Die-cast aluminium
Material bowl	PC