


Service unit combination MSB6-AGF:J1:M1-WP

Part number: 8233048

FESTO



Data sheet

Feature	Value
Size	6
Series	MS
Actuator lock	Rotary knob with detent can be closed with accessories
Mounting position	Vertical +/-5°
Condensate drain	Manually rotating
Design	Filter/Closed-loop controller/lubricator
Max. condensate volume	38 ml
Grade of filtration	40 µm
Max. oil capacity	75 cm³
Controller function	Output pressure constant Via primary pressure compensation With secondary venting With return flow function
Bowl guard	Plastic bowl guard
Pressure gauge (ANALOG) or Pressure display (DIGITAL)	With pressure gauge
Operating pressure	0.15 MPa...2 MPa 1.5 bar...20 bar
Pressure regulation range	0.5 bar...12 bar
Max. standard flow rate	3700 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [-:4:-] Inert gases
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air purity class at output	Compressed air to ISO 8573-1:2010 [7:4:-]
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	1930 g
Type of mounting	Via mounting bracket
Pneumatic connection, port 1	G1

Feature	Value
Pneumatic connection, port 2	G1
Material seals	NBR
Material filter	PE
Material housing	Die-cast aluminium
Material bowl	PC