

Bulkhead quick connector SCK-PK-9-KU

Part number: 9390

FESTO



Data sheet

Feature	Value
Nominal size	8 mm
Mounting position	optional
Design	Bulkhead
Operating pressure complete temperature range	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Pneumatic connection, port 1	For barbed fitting inside diameter of 9 mm with union nut
Pneumatic connection, port 2	For barbed fitting inside diameter of 9 mm with nut
Material union nut	POM
Note on materials	RoHS-compliant
Material nut	POM
Material connector	POM