

Adapter
AD-G1/2-1/2NPT-I
Part number: 9398

FESTO



Data sheet

Feature	Value
Nominal size	14.3 mm
Operating pressure complete temperature range	-0.95 bar...10 bar
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Max. tightening torque pneumatic connection 1	40 Nm
Max. tightening torque pneumatic connection 2	28 Nm
Nominal torque	47.9 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	51.89 g
Pneumatic connection, port 1	Male thread G1/2
Pneumatic connection, port 2	Female thread 1/2 NPT
Note on materials	RoHS-compliant
Material seals	PVC
Material housing	Galvanised steel