

# Flow control/silencer GRU-1/2-B

Part number: 9519

FESTO



## Data sheet

| Feature                                             | Value                                     |
|-----------------------------------------------------|-------------------------------------------|
| Valve function                                      | Sound pressure control function           |
| Selection of additional functions                   | With silencer                             |
| Pneumatic connection, port 1                        | G1/2                                      |
| Adjustment component                                | Slotted head screw                        |
| Type of mounting                                    | Screw-in                                  |
| Standard flow rate 0.6->0 MPa (6->0 bar, 87->0 psi) | 0 l/min...4000 l/min                      |
| Ambient temperature                                 | -10 °C...70 °C                            |
| Material housing                                    | Aluminium                                 |
| Mounting position                                   | optional                                  |
| Operating pressure complete temperature range       | 0 bar...10 bar                            |
| Operating medium                                    | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Note on operating and pilot medium                  | Lubricated operation possible             |
| LABS (PWIS) conformity                              | VDMA24364-B1/B2-L                         |
| Media temperature                                   | -10 °C...70 °C                            |
| Product weight                                      | 100 g                                     |
| Material shock absorber insert                      | PE                                        |
| Material screwed plug                               | Die-cast aluminium                        |
| Note on materials                                   | RoHS-compliant                            |
| Material adjusting screw                            | PA                                        |