


# Short pulse valve VLK-3-PK-3

Part number: 9639



## Data sheet

| Feature                                               | Value                                                                                                                      |
|-------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------|
| Nominal size                                          | 2.5 mm                                                                                                                     |
| Operating pressure                                    | 2.5 bar...8 bar                                                                                                            |
| Standard nominal flow rate (standardised to DIN 1343) | 90 l/min                                                                                                                   |
| Explosion protection                                  | The information in the certificate must be observed!<br>Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX) |
| LABS (PWIS) conformity                                | VDMA24364-B1/B2-L                                                                                                          |
| Ambient temperature                                   | -10 °C...60 °C                                                                                                             |
| Product weight                                        | 170 g                                                                                                                      |
| Type of mounting                                      | On mounting frame                                                                                                          |
| Material seals                                        | TPE-U(PU)                                                                                                                  |
| Material housing                                      | Die-cast zinc                                                                                                              |