


Pneumatic limit valve
RWN/O-3-1/8-B
Part number: 9694



Data sheet

Feature	Value
Valve function	3/2-way, monostable, open/closed
Standard nominal flow rate (standardised to DIN 1343)	120 l/min
pneumatic working port	G1/8
Operating pressure	-0.95 bar...8 bar
LABS (PWIS) conformity	VDMA24364-B2-L