


# Quick exhaust valve SEU-1/8-NPT

Part number: 9798

**FESTO**



## Data sheet

| Feature                                                                    | Value                                                                                      |
|----------------------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| Valve function                                                             | Quick exhaust                                                                              |
| Selection of additional functions                                          | With silencer                                                                              |
| Pneumatic connection, port 1                                               | 1/8 NPT                                                                                    |
| Pneumatic connection, port 2                                               | 1/8 NPT                                                                                    |
| Type of mounting                                                           | Screw-in                                                                                   |
| Standard nominal flow rate, exhaust 0.6->0.5 MPa (6->5 bar, 87->72.5 psi)  | 390 l/min                                                                                  |
| Standard nominal flow rate, exhaust 0.6->0 MPa (6->0 bar, 87->0 psi)       | 1000 l/min                                                                                 |
| Standard nominal flow rate, air flow 0.6->0,5 MPa (6->5 bar, 87->72.5 psi) | 300 l/min                                                                                  |
| Operating pressure                                                         | 0.5 bar...10 bar                                                                           |
| Ambient temperature                                                        | -20 °C...75 °C                                                                             |
| Operating medium                                                           | Compressed air to ISO 8573-1:2010 [7:-:-]                                                  |
| Nominal size                                                               | 5 mm                                                                                       |
| Note on operating and pilot medium                                         | Lubricated operation possible (in which case lubricated operation will always be required) |
| LABS (PWIS) conformity                                                     | VDMA24364-B1/B2-L                                                                          |
| Media temperature                                                          | -20 °C...75 °C                                                                             |
| Sound pressure level                                                       | 86 dB(A)                                                                                   |