

Indicating insert
MFL-24DC/AC
Part number: 10004

FESTO



Data sheet

Feature	Value
Product weight	15 g
Electrical connection	Form B As per industrial standard (11 mm)
Nominal operating voltage DC	24 V
Nominal operating voltage AC	24 V
Mains frequency	0 Hz...60 Hz
Permissible voltage fluctuations	+/- 15 %
Degree of protection	IP65 as per IEC 60529
Ambient temperature	-20 °C...60 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	PA6-reinforced