

Exhaust air flow control valve GRE-1/8-NPT

Part number: 10057

FESTO



Data sheet

| Feature | Value |
|------------------------------------------|--------------------------------------------------------------------|
| Valve function | Sound pressure flow control function |
| Selection of additional function | with muffler |
| Pneumatic connection 1 | 1/8 NPT |
| Adjusting element | Slotted screw |
| Type of mounting | Screw-in |
| Standard flow rate 6->0 bar | 0 l/min...520 l/min |
| Operating pressure | 0 bar...10 bar |
| Ambient temperature | -10 °C...70 °C |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:::] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | -10 °C...70 °C |
| Note on materials | RoHS-compliant |